



HR441

EARTH LEAK REL 0.03-3A DELAY TORR 35

Product Datasheet

Main electrical features

Frequency	50/60 Hz
Rated operational voltage Ue	230 V

Voltage

Max operating voltage	276 V
Rated impulse withstand voltage	4 kV

Electric current

Acceptable current rating with AC1	8 A
Rated residual operating current	30/100/300/500/1000/3000 mA
Torroïds : Allowed overload	30kA, 100ms

Length

Maximum connection distance between receiver and transmitter	25m and 50m twisted pair
--	--------------------------

Power

Power consumed	10 VA
Total power loss under IN	4 W

Dimensions

Depth of installed product	65 mm
----------------------------	-------

Installation, mounting

Tightening torque	1 Nm
-------------------	------

Connection

Connection cross-section in flexible cable for the measurement	1 to 2,5 mm ²
Connection cross-section in massive cable for the measurement	1,5 to 4 mm ²
Connection cross-sect. rigid cable	1,5 / 4mm ²
Connection cross-sect. flexible conductor	1 / 2,5mm ²
Type of contacts	Stand 1 OF

Settings

Delay adjustable	yes
Time delay of residual current	0/0,1/0,3/0,5/0,75/1 s

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP30
Residual current type	A

Use conditions

Altitude	2000 m
Storage temperature	-25 to 70 °C
