



LS404

Fuse carrier 3P+N 25A L31 4M

Product Datasheet

Architecture

Type of pole	3P+N
--------------	------

Voltage

Rated insulation voltage	690 V
--------------------------	-------

Electric current

Rated current	25 A
---------------	------

Fuse

CharactFuse	gG, aM
-------------	--------

Power

Total power loss under IN	12,2 W
---------------------------	--------

Dimensions

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	72 mm

Installation, mounting

Tightening torque	2,2Nm
-------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C