



HEC126H

MCCB h250 4P 70kA 125A LSI

Product Datasheet

Architecture

Type of order	Toggle
Number of poles	4 P
Type of pole	4P4D N:0/50/100%

Functions

Complete device with protection unit	yes
Trip Unit	LSI
Integrated earth fault protection	no

Compatibility

Compatible with DIN rail mounting	no
-----------------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	no

Electric current

Rated current	125 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0,4 / 0,5 / 0,63 / 0,8 / 0,9 / 0,95 / 1
Thermal setting current on neutral pole	0 / 0,5 / 1 In
Breaking capacity on 1 pole for IT 230V NF 60947-2	51 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	71 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	50 kA

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

Power

Total power loss under I _N	18,3 W
Power loss per pole at I _N	6,1 W

Tripping

Trip mode	LSI
Thermal protection trip time	5 / 8 / 11 / 21 ms
Time of response when opening	10 ms

Electrical specifications

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	12Nm
DIN rail mounting with optional adaptor	no

Connection

Connection cross-sect. flexible conductor	35 / 150mm ²
Connection cross-sect. rigid cable	35 / 185mm ²
Connection	Front connection
Type of connection	Terminal

Settings

Range of the magnetic adjustment	700 / 882 / 1120 / 1400 / 1610 / 1680 / 1750 A
Magnetic protection nob setting xI _N	2,5 / 5 / 10
Setting type I _N or I _{th}	I _{th}

Equipment

Motor drive optional	yes
----------------------	-----

Use cases

Category of use	A
-----------------	---

Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C