

RCCB 2P 25A 300mA HI

Product Datasheet

Architecture

Neutral position	left
Number of poles	2 P
Fixing mode	Din-Rail

Controls and indicators

Ground fault signalisation	yes
----------------------------	-----

Main electrical features

Frequency	50 Hz
Rated operational voltage Ue	230 V

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	300 mA
Withstand not tripping on 8-20 μ s wave	3 kA
Breaking and opening capacity	1,5 kA
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA

Electric current / temperature

Rating current -15°C	25 A
Rating current -20°C	25 A
Rating current 0°C	25 A
Rating current 10°C	25 A
Rating current -10°C	25 A
Rating current 15°C	25 A
Rating current 20°C	25 A
Rating current 25°C	25 A
Rating current -25°C	25 A
Rating current 30°C	25 A
Rating current 35°C	25 A
Rating current 40°C	25 A
Rating current 45°C	25 A
Rating current 5°C	25 A
Rating current -5°C	25 A
Rating current 50°C	25 A
Rating current 55°C	25 A
Rating current 60°C	25 A
Rating current 65°C	25 A
Rating current 70°C	21 A

Power

Power loss per pole at In	0,7 W
Total power loss under IN	1,3 W

Tripping

Short-time delayed tripping	no
Protected against nuisance tripping	yes

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	4000

Dimensions

Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm
Construction size (DIN 43880)	1

Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of bottom rail clip for modular devices	metallic
Type of top rail clip for modular devices	NA
Type of Bottom Connection for modular devices	Blconnect
Bottom removability for modular devices	no
Top removability for modular devices	no

Connection

Connection cross-section of the access with screws, with flexible conductor	1/16 mm ²
Connection cross-section at output with screw, for massive conductor	1/25 mm ²
Connection cross-section for rigid conductor, upstream terminals with screws	1/25 mm ²
Connection cross-sect. rigid cable	25mm ²
Connection cross-sect. flexible conductor	16mm ²
Type of connection	with screw
Connection cross section of access and exit with screws, for flexible conductor	1/16 mm ²

Standards

Standard text	EN 61008-1
European directive WEEE	concerned

Safety

Protection index IP	IP20
Residual current type	HI

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-25 ... 40 °C
Altitude	2000 m
Storage temperature	-55 to 70 °C
Air humidity protection	Execution I
Storage/transport temperature	-55 ... 70 °C