



VE110L

Encl., vector, IP5x, 10M, version AUT

Technische Merkmale

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead yes

Compatibility

Compatible with DIN rail mounting yes

Main electrical features

Nominal voltage 400 V

Cover, door

Cover type Closed (plain)

Transparent cover or door yes

Cover type Door

Door locking without

Type of door closing Latch

Door leave single

Door quantity 1

Identification od protection index 55

Interlockable no

Materials

RAL colour RAL 7035 - Light grey

Colour light grey

Colour light grey

Material plastic

Enclosure material polystyrene

Type of surface treatment untreated

Dimensions

Depth of installed product 114 mm

Internal depth 114 mm

Height of installed product 210 mm

Width of installed product 237 mm

Width in division units 10

Thickness of sidewall material 2,5 mm

Installation, mounting

Suitable for outdoor use yes

Connection

Number of conduit inlets 6

Accessories included

| | |
|-------------------------|----|
| Mounting plate included | no |
| With lock | no |

Equipment

| | |
|--------------------------------------|-----|
| Number of openings for flange plates | 20 |
| Number of rows | 1 |
| Quantity of section in width | 1 |
| Can be accessorized | yes |
| Quantity of rails | 1 |

Standards

| | |
|-------------------------|-----------|
| GWT Glow wire test | 750 °C |
| European directive WEEE | concerned |

Safety

| | |
|---|---------------|
| Protection class | isol.class II |
| Protection index IP | IP55 |
| IK protection code against mechanical impacts | IK07 |
| Halogen free | yes |
| Ultraviolet resistant | yes |

Use conditions

| | |
|-----------------------|---------------|
| Operating temperature | -25 ... 40 °C |
|-----------------------|---------------|