



85146173



IP20

## HBNet F-TA 2k LI K5 E-STAHL

### Technische Merkmale

#### Functions

- ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
- Configurable transmission and/or reception behaviour
- reset function (to factory setting)
- easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
- scene saving lockable
- quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

#### Controls and indicators

- operating areas configurable as one or two-area operation
- with configuration and function button

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Frequency

Radio transmission/reception frequency	868,3 MHz
--	-----------

#### Power

Radio transmission power	< 10 mW
- low intrinsic energy requirement	

#### Measurement

Relative humidity (without condensation)	0 ... 65 % (without condensation)
--	-----------------------------------

#### Materials

RAL colour	RAL 9022 - Pearl light grey
Colour of design line	stainless steel
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

#### LED control

- with configuration and function LEDs
- LED application module/insert compatibility display

#### Connection

- integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

#### Settings

- top and bottom operating areas on 2gang switching/dimming inserts and network insert are freely configurable
- toolless quicklink configuration using buttons and LED display

---

**Equipment**

---

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %
- switch-on brightness level for each operating area on configuration with dimmer insert, power failure proof, storable	

---

**Safety**

- 
- with dismantling protection
- 

**Use conditions**

---

Operating temperature	-5 ... 45 °C
-----------------------	--------------

---

**Identification**

---

Application, usage	Light control, KNX radio- operating systems
Secondary design line(s)	Berker.Net, Berker K.5

---