



ESC465

Contactors 63A, 2NO+2NC, 230V

Product Datasheet

Architecture

Type of order	Not applicable
Number of poles	4 P

Main electrical features

Frequency	50 Hz
Rated operational voltage Ue	400 V

Voltage

Rated insulation voltage	440 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

Electric current

Acceptable current load with AC7 category A	63 A
Acceptable current load with AC7 category B	32 A
Thermal rated current outside of housings	63 A

Power

Inrush power absorbed	62,5 W
Operating consumption	5,75 W
Contact rating with 230 V in AC7 category A	11,6 kW
Contact rating with 230 V in AC7 category B	3,3 kW
Contact rating with 400 V in AC7 category A	35 kW
Contact rating with 400 V in AC7 category B	7,8 kW
Power loss per contact	5 W
Total power loss under I _N	25,75 W
Power dissipation per coil	0,5 W

Tripping

Time of response when closing	25 ms
Time of response when opening	20 ms

Resistance

Winding resistance	770 Ω
--------------------	-------

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

Dimensions

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

Fluorescent bulbs control

Max. load fluorescent lamp	3000 VA
Max. power with fluorescent parallel lamps	2100 VA
Fluorescent lamps in duo circuit	4700 VA

Incandescent bulbs control

Max. power with incandescent lamps	6500 W
------------------------------------	--------

Installation, mounting

Tightening torque	Coil: 2,5Nm, Power: 3,5Nm
-------------------	---------------------------

Connection

Max cable connect. cross section (flexible) for control	1 to 6 mm ²
Connection cross-section of the control cable solid	1 to 10 mm ²
Connection cross-sect. rigid cable	4 / 25mm ²
Connection cross-sect. flexible conductor	4 / 16mm ²
Type of connection	with screw
Number of contacts	4
Type of contacts	2NC+2NO

Equipment

Can be accessorized	yes
---------------------	-----

Use

Local operation/hand operation	no
--------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
Protection index IP	2

Use conditions

Storage temperature	-40 to 80 °C
---------------------	--------------