



LR602

Fuse carrier 2P 50A L51 3M

Product Datasheet

Architecture

| | |
|-----------------|-----|
| Number of poles | 2 P |
| Type of pole | 2 P |

Electric current

| | |
|---------------|------|
| Rated current | 50 A |
|---------------|------|

Fuse

| | |
|-------------|--------|
| CharactFuse | gG, aM |
|-------------|--------|

Power

| | |
|---------------------------------------|--------|
| Total power loss under I _N | 12,5 W |
|---------------------------------------|--------|

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 93 mm |
| Height of installed product | 107 mm |
| Width of installed product | 52,5 mm |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|--|-------------|
| Operating temperature | -5...40 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 3 |
| Storage/transport temperature | -25...80 °C |