



HNG200U

## MCCB h250 3P 50kA 200A TM

Product Datasheet

### Architecture

Type of order	Toggle
Number of poles	3 P
Type of pole	3P3D

### Functions

Complete device with protection unit	yes
Trip Unit	TM A/A
Integrated earth fault protection	no

### Compatibility

Compatible with DIN rail mounting	no
-----------------------------------	----

### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	no

### Electric current

Rated current	200 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	7,5 kA
Thermal protection nob setting xIN	0,63 / 0,8 / 1
Breaking capacity on 1 pole for IT 230V NF 60947-2	51 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	50 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	50 kA

### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

### Power

Total power loss under I <sub>N</sub>	31,2 W
Power loss per pole at I <sub>N</sub>	10,4 W

### Tripping

Trip mode	TM
Time of response when opening	20 ms

### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

### Installation, mounting

Tightening torque	12 Nm
DIN rail mounting with optional adaptator	no

### Connection

Connection cross-sect. flexible conductor	35 / 150 mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185 mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal

### Settings

Range of the magnetic adjustment	1200 / 1600 / 2000 / 2600 A
Magnetic protection nob setting x I <sub>N</sub>	6 / 8 / 10 / 13
Setting type I <sub>N</sub> or I <sub>th</sub>	I <sub>N</sub>

### Equipment

Motor drive optional	yes
----------------------	-----

### Use cases

Category of use	A
-----------------	---

### Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

### Safety

Protection index IP	IP4X
---------------------	------

Use conditions

Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C