



LS771

Microswitch 3P for fuse carrier L58

Product Datasheet

Architecture

Number of poles	3 P
-----------------	-----

Compatibility

Suitable for	Fuse carrier
--------------	--------------

Main electrical features

Rated operational voltage Ue	220 / 250 V
Frequency	40/60 Hz

Voltage

Rated insulation voltage	6000 V
Rated operational voltage in DC	24 / 220 V

Electric current

Acceptable current rating with AC1	5 A
Imin = f (U = 230 V AC)	5 A

Fuse

Fuse Size	22 x 58
-----------	---------

Dimensions

Width of installed product	9 mm
----------------------------	------

Connection

Type of connection	fast-on terminal
--------------------	------------------

Accessories included

Type of accessory	fault-signal contact
-------------------	----------------------

Equipment

Quantity of INV contacts	1
--------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-5...40 °C
Air humidity protection	95% / 80°C
Storage/transport temperature	-25...55 °C