



HEC125H

**MCCB h250 3P 70kA 125A LSI**

Product Datasheet

**Architecture**

Type of order	Toggle
Number of poles	3 P
Type of pole	3P3D

**Functions**

Complete device with protection unit	yes
Trip Unit	LSI
Integrated earth fault protection	no

**Compatibility**

Compatible with DIN rail mounting	no
-----------------------------------	----

**Main electrical features**

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	no

**Electric current**

Rated current	125 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0,4 / 0,5 / 0,63 / 0,8 / 0,9 / 0,95 / 1
Breaking capacity on 1 pole for IT 230V NF 60947-2	51 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	71 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	50 kA

**Current correction factors**

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

**Power**

Total power loss under IN	18,3 W
Power loss per pole at In	6,1 W

**Tripping**

Tripmode	LSI
Thermal protection trip time	5 / 8 / 11 / 21 ms
Time of response when opening	10 ms

**Electrical specifications**

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Installation, mounting**

Tightening torque	12Nm
DIN rail mounting with optional adaptator	no

**Connection**

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal

**Settings**

Range of the magnetic adjustment	700 / 882 / 1120 / 1400 / 1610 / 1625 / 1625 A
Magnetic protection nob setting xIN	2,5 / 5 / 10
Setting type In or Ith	IrTh

**Equipment**

Motor drive optional	yes
----------------------	-----

**Use cases**

Category of use	A
-----------------	---

**Standards**

Standard text	IEC 60947-2
European directive WEEE	concerned

**Safety**

Protection index IP	IP4X
---------------------	------

**Use conditions**

Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C