



ESC466

Contactor 63A, 3NO+1NC, 230V

Product Datasheet

Architecture

Type of order	Not applicable
Number of poles	4 P

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	440 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	63 A
Thermal rated current outside of housings	63 A
Acceptable current load with AC7 category A	63 A
Acceptable current load with AC7 category B	32 A

Power

Inrush power absorbed	62,5 W
Operating consumption	5,75 W
Total power loss under IN	25,75 W
Power loss per contact	5 W
Power dissipation per coil	0,5 W
Contact rating with 230 V in AC7 category A	11,6 kW
Contact rating with 230 V in AC7 category B	3,3 kW
Contact rating with 400 V in AC7 category A	35 kW
Contact rating with 400 V in AC7 category B	10 kW

Tripping

Time of response when opening	20 ms
Time of response when closing	25 ms

Resistance

Winding resistance	770 Ω
--------------------	-------

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

Dimensions

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	2100 VA
Fluorescent lamps in duo circuit	4700 VA
Max. load fluorescent lamp	3000 VA

Incandescent bulbs control

Max. power with incandescent lamps	6500 W
------------------------------------	--------

Installation, mounting

Tightening torque	Coil: 2,5Nm, Power: 3,5Nm
-------------------	---------------------------

Connection

Connection cross-sect. flexible conductor	1,5 / 16mm ²
Connection cross-sect. rigid cable	1,5 / 25mm ²
Number of contacts	4
Type of contacts	3NO+1NC
Type of connection	with screw
Cable connect. cross section (flexible) for control	1 / 2,5 mm ²
Connection cross-section of the control cable solid	1 / 2,5 mm ²

Equipment

Can be accessorized	yes
With slide for manual switch	no

Use

Local operation/hand operation	no
--------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP2X
Protection class	isol.class II

Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C