



WS155

Systo Cable outlet

Product Datasheet

Architecture

| | |
|--------------|----------|
| Type of pole | 0 P |
| Fixing mode | Recessed |

Functions

| | |
|------------------------|----|
| Overvoltage protection | no |
|------------------------|----|

Controls and indicators

| | |
|---------------------------|---------|
| Indicator lamp | no |
| With or without indicator | without |

Connectivity

| | |
|--------------------------|----|
| With USB charging socket | no |
|--------------------------|----|

Main electrical features

| | |
|-----------------|----------|
| Frequency | 50/60 Hz |
| Nominal voltage | 400 V |

Capacity

| | |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

Cover, door

| | |
|---------------|----|
| Interlockable | no |
|---------------|----|

Power supply

| | |
|----------------------|-------------------------|
| Special power supply | No special power supply |
|----------------------|-------------------------|

Materials

| | |
|---------------------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
| Material | Polycarbonate (PC) |
| Surface appearance | satın finish |
| Type of surface treatment | Painted |

Dimensions

| | |
|-----------------------------|----------|
| Depth of installed product | 22,8 mm |
| Height of installed product | 45 mm |
| Length | 37 mm |
| Width of installed product | 45 mm |
| Dimensions (LLxwwxhh) | 45x45x37 |

Installation, mounting

| | |
|---------------|---------|
| Fixing type | Clipped |
| Mounting type | various |

Connection

| | |
|--------------------|------------|
| Type of connection | with screw |
| Phase pickup | L1 |

Equipment

| | |
|---------------|----|
| On/Off switch | no |
|---------------|----|

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

Safety

| | |
|---|---------------------------------|
| Protection index IP | 21D |
| IK protection code against mechanical impacts | 07 |
| Glow wire test | according to CEI 695-2-1: 650°C |

Identification

| | |
|---------|-------|
| Range | systo |
| Version | Other |