



VE106PN

Encl., vector, surface m., IP65,6M

Technische Merkmale

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	yes
---------------------	-----

Compatibility

Compatible with DIN rail mounting	yes
-----------------------------------	-----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

Cover, door

Cover type	Closed (plain)
------------	----------------

Transparent cover or door	yes
---------------------------	-----

Cover type	Door
------------	------

Door locking	without
--------------	---------

Type of door closing	Latch
----------------------	-------

Door leave	single
------------	--------

Door quantity	1
---------------	---

Identification od protection index	65
------------------------------------	----

Interlockable	no
---------------	----

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Colour	light grey
--------	------------

Colour	light grey
--------	------------

Material	plastic
----------	---------

Enclosure material	polycarbonate
--------------------	---------------

Type of surface treatment	untreated
---------------------------	-----------

Dimensions

Depth of installed product	113 mm
----------------------------	--------

Internal depth	113 mm
----------------	--------

Height of installed product	190 mm
-----------------------------	--------

Width of installed product	165 mm
----------------------------	--------

Width in division units	6
-------------------------	---

Thickness of sidewall material	2,5 mm
--------------------------------	--------

Installation, mounting

Suitable for outdoor use	yes
--------------------------	-----

Connection

Number of conduit inlets	3
--------------------------	---

Accessories included

Mounting plate included	no
With lock	no

Equipment

Number of openings for flange plates	16
Number of rows	1
Quantity of section in width	1
Can be accessorized	yes
Quantity of rails	1

Standards

GWT Glow wire test	850 °C
European directive WEEE	concerned

Safety

Protection class	isol.class II
Protection index IP	IP65
IK protection code against mechanical impacts	IK07
Halogen free	yes
Ultraviolet resistant	yes

Use conditions

Operating temperature	-25 ... 40 °C
-----------------------	---------------

Identification

Range name	vector
------------	--------