



VE110PN

Encl., vector, flush m., IP65,10M

Technische Merkmale

### Architecture

Fixing mode surface-mounting

### Functions

With a pipe-in lead yes

### Compatibility

Compatible with DIN rail mounting yes

### Main electrical features

Nominal voltage 400 V

### Voltage

Rated operational voltage in DC 1000 V DC

### Cover, door

Cover type Closed (plain)

Transparent cover or door yes

Cover type Door

Door locking without

Type of door closing Latch

Door leave single

Door quantity 1

Identification od protection index 65

Interlockable no

### Materials

RAL colour RAL 7035 - Light grey

Colour light grey

Colour light grey

Material plastic

Enclosure material polycarbonate

Type of surface treatment untreated

### Dimensions

Depth of installed product 114 mm

Internal depth 114 mm

Height of installed product 210 mm

Width of installed product 237 mm

Width in division units 10

Thickness of sidewall material 2,5 mm

### Installation, mounting

Suitable for outdoor use yes

**Connection**

Number of conduit inlets	6
--------------------------	---

**Accessories included**

Mounting plate included	no
With lock	no

**Equipment**

Number of openings for flange plates	20
Number of rows	1
Quantity of section in width	1
Can be accessorized	yes
Quantity of rails	1

**Standards**

GWT Glow wire test	850 °C
European directive WEEE	concerned

**Safety**

Protection class	isol.class II
Protection index IP	IP65
IK protection code against mechanical impacts	IK07
Halogen free	yes
Ultraviolet resistant	yes

**Use conditions**

Operating temperature	-25 ... 40 °C
-----------------------	---------------

**Identification**

Range name	vector
------------	--------