



TXA114



Power supply 1x 30V DC + 1x 24V DC

Technische Merkmale

Architecture

Bus system	EIB
Fixing mode	Din-Rail

Connectivity

Bus lines	1
- one output 30 V DC, 320 mA incl. choke	
- one output 24 V, 640 mA	

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	24V+30V
Output voltage	28...32 V

Electric current

Output current	max. 320 mA
Output intensity	320 mA

Fuse

Fuse	with electronic short-circuit and overload protection
------	---

Power

Total power loss under IN	4,4 W
---------------------------	-------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm
Width of rail mounted device (RMD)	4 modules

LED control

LED	with green LED for display of power supply per output, with red LED for display of short-circuit and overload protection per output
-----	---

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Conductor cross-section (flexible)	0,75...2,5 mm ²
Conductor cross-section (rigid)	0,75...2,5 mm ²
Connection	protected earth conductor must be connected
- with QuickConnect plug-in terminals	

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C