



VE106L

Encl., vector, IP5x, 6M, version AUT

Technische Merkmale

Architecture

| | |
|-------------|------------------|
| Fixing mode | surface-mounting |
|-------------|------------------|

Functions

| | |
|---------------------|-----|
| With a pipe-in lead | yes |
|---------------------|-----|

Compatibility

| | |
|-----------------------------------|-----|
| Compatible with DIN rail mounting | yes |
|-----------------------------------|-----|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 400 V |
|-----------------|-------|

Cover, door

| | |
|------------|----------------|
| Cover type | Closed (plain) |
|------------|----------------|

| | |
|---------------------------|-----|
| Transparent cover or door | yes |
|---------------------------|-----|

| | |
|------------|------|
| Cover type | Door |
|------------|------|

| | |
|--------------|---------|
| Door locking | without |
|--------------|---------|

| | |
|----------------------|-------|
| Type of door closing | Latch |
|----------------------|-------|

| | |
|------------|--------|
| Door leave | single |
|------------|--------|

| | |
|---------------|---|
| Door quantity | 1 |
|---------------|---|

| | |
|------------------------------------|----|
| Identification od protection index | 55 |
|------------------------------------|----|

| | |
|---------------|----|
| Interlockable | no |
|---------------|----|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 7035 - Light grey |
|------------|-----------------------|

| | |
|--------|------------|
| Colour | light grey |
|--------|------------|

| | |
|--------|------------|
| Colour | light grey |
|--------|------------|

| | |
|----------|---------|
| Material | plastic |
|----------|---------|

| | |
|--------------------|-------------|
| Enclosure material | polystyrene |
|--------------------|-------------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

Dimensions

| | |
|----------------------------|--------|
| Depth of installed product | 113 mm |
|----------------------------|--------|

| | |
|----------------|--------|
| Internal depth | 113 mm |
|----------------|--------|

| | |
|-----------------------------|--------|
| Height of installed product | 190 mm |
|-----------------------------|--------|

| | |
|----------------------------|--------|
| Width of installed product | 165 mm |
|----------------------------|--------|

| | |
|-------------------------|---|
| Width in division units | 6 |
|-------------------------|---|

| | |
|--------------------------------|--------|
| Thickness of sidewall material | 2,5 mm |
|--------------------------------|--------|

Installation, mounting

| | |
|--------------------------|-----|
| Suitable for outdoor use | yes |
|--------------------------|-----|

Connection

| | |
|--------------------------|---|
| Number of conduit inlets | 3 |
|--------------------------|---|

Accessories included

| | |
|-------------------------|----|
| Mounting plate included | no |
| With lock | no |

Equipment

| | |
|--------------------------------------|-----|
| Number of openings for flange plates | 16 |
| Number of rows | 1 |
| Quantity of section in width | 1 |
| Can be accessorized | yes |
| Quantity of rails | 1 |

Standards

| | |
|-------------------------|-----------|
| GWT Glow wire test | 750 °C |
| European directive WEEE | concerned |

Safety

| | |
|---|---------------|
| Protection class | isol.class II |
| Protection index IP | IP55 |
| IK protection code against mechanical impacts | IK07 |
| Halogen free | yes |
| Ultraviolet resistant | yes |

Use conditions

| | |
|-----------------------|---------------|
| Operating temperature | -25 ... 40 °C |
|-----------------------|---------------|