



85745226



IP20

## HBNet FUNK-ZSU LI Q1 ANTH MATT

### Technische Merkmale

### Functions

Astronomic time shift	± 2 h
Random number generator	± 15 mn
Power reserve	≈ 8 h
<ul style="list-style-type: none"> <li>- ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display</li> <li>- reset function (to factory setting)</li> <li>- Configurable transmission and/or reception behaviour</li> <li>- Party function, no execution of automatic, radio and extension unit commands (switch protection)</li> <li>- with keylock</li> <li>- easy additional functions: +6 scenes, dimming, 1 up/down button control, priority</li> <li>- quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control</li> <li>- with switchover manual/automatic mode</li> </ul>	

### Controls and indicators

- LC display illuminated during operation
- indication of the application module/insert compatibility in the display
- LC display contrast is adjustable

### Connectivity

Radio protocol	KNX Radio
----------------	-----------

### Power

Radio transmission power	< 10 mW
--------------------------	---------

### Measurement

Relative humidity (without condensation)	0...65 % (without condensation)
Running accuracy	± 3 min/year

### Materials

Colour of design line	anthracite
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

### Connection

- integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

### Settings

Time	with automatic summer-/winter time switching (can be switched off)
<ul style="list-style-type: none"> <li>- astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable</li> <li>- standalone programme, radio and extension unit commands are not executed</li> <li>- holiday programme for random variation of the switching times in automatic operation</li> </ul>	

#### Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Number of switching times for on/off	20
- 2 independent preset programme memories, individually adaptable	

#### Use

Differentiation characteristic 2 - Sales	with display
--	--------------

#### Safety

Protection index IP	IP20
- with dismantling protection	

#### Use conditions

Operating temperature	-5...45 °C
- low intrinsic energy requirement	

#### Identification

Application, usage	Light control, KNX radio- operating systems
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9