



85345173



IP20

HBNet WÄCH F-QUICKL 1,1m K5 E-STAHL

Technische Merkmale

Functions

- μ -processor controlled mode of operation
- ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value, brightness display, movement scene loading, no movement scene loading
- reset function (to factory setting)
- Party function for switching on for 2 hours
- with memory function for presence simulation
- with keylock
- Switch-off pre-warning on dimmer inserts
- Teach function for response brightness via button
- scene opening via KNX radio appliances
- scene saving lockable
- quicklink functions: switching, dimming, 2 scenes, time switching, NO contact push-button, Memory, forced control, Master-Slave

Compatibility

- optional operation of extension units using installation push-button

Controls and indicators

- remote control via quicklink transmitter
- with configuration and function button
- with button for on/off/automatic/memory/party function

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Frequency

Radio transmission frequency	868,3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Relative humidity (without condensation)	0...65 % (without condensation)
Detection field, rectangular shaped	$\approx 12 \times 16 \text{ m}$

Reach distance

Range, frontal	$\approx 12 \text{ m}$
Range, side	each $\approx 8 \text{ m}$

Detection

Number of detection levels	2
Detection angle, settable	each side $\approx 45...90^\circ$

Materials

Colour of design line	stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

Dimensions

Assembling height	34 mm
Nominal mounting height	1,1 m

Lighting control

Response brightness, adjustable	≈ 5...1000 lx , daytime operation
---------------------------------	-----------------------------------

LED control

LED	LED application module/insert compatibility display, with configuration and function LEDs, with operation and status LED, red/green/orange
-----	--

Connection

- integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
--

Settings

Response sensitivity, settable	10...100 %
Delay time, adjustable	≈ 1 s...3 h
Switch-off pre-warning to dimming value 50% for	30 s

Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

Safety

- with dismantling protection

Use conditions

Operating temperature	-5...45 °C
- low intrinsic energy requirement	

Identification

Application, usage	Motion detector, KNX radio- sensors
Main design line	Berker K.5
Secondary design line(s)	Motion detector, Berker.Net, Berker K.5

Instructions

Information text	Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!
------------------	---