



SVN391

## Impulse 1NO + 1NC Double Pushbutton

Product Datasheet

### Main electrical features

Rated operational voltage U <sub>e</sub>	230 V
Frequency	50/60 Hz

### Voltage

Rated insulation voltage	250 V
Rated impulse withstand voltage	4000 V
Switching voltage	230 V

### Electric current

Rated current	16 A
Momentary-contact current	16 A
Prospective short circuit withstand with MCB 16A B curve	1000A [Prot:16AcurveB]
Prospective short circuit withstand with fuse 16A gG	1000A [Prot:16AgG]
Thermal rated current outside of housings	16 A

### Endurance

Electric endurance in number of cycles	15000
Number of mechanical operations	15000

### Materials

Colour	not applicable
--------	----------------

### Dimensions

Depth of installed product	66 mm
Height of installed product	83 mm
Width of installed product	17,5 mm

### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

### Connection

Connection cross-sect. flexible conductor	0,75 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 10mm <sup>2</sup>
Type of connection	with screw

### Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1

### Standards

European directive WEEE	concerned
-------------------------	-----------

## Safety

Protection index IP	IP20
---------------------	------

## Use conditions

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Storage/transport temperature	-40...80 °C